

Armytek Viking Pro v3 / XHP50 White Tactical flashlight

SKU: F01903BC | EAN-13: 6957713001463

Detailed description:

- amazing light output of 2300 LED lumens and excellent range up to 286 meters;
- clear central spot and side light 10°:80°;
- trouble-free operation of the flashlight at a depth of 50 meters for 5 hours;
- the maximum possible continuous operation time on a single charge;
- the original remote button for easy hunting;
- record time up to 200 days;
- the flashlight easily withstands a fall from a height of 30 meters, the recoil of 12-gauge weapons, works at a depth of 50 meters under water;
- IP68 water- and dustproof standard.

Additional features:

LED: Cree XHP50

Power source: 1x18650 Li-Ion / 2x18350 Li-Ion* / 2xRCR123 Li-Ion* / 2xCR123A

Number of modes: 9

Length: 154mm

Body diameter: 25.4mm

Head diameter: 41mm

Weight (without batteries): 126g

Package Set: flashlight, 2 rubber rings, rubber grip, holster, lanyard, 2 O-rings, spare rubber button, user manual

Manufacturer warranty: 10 years no-hassle warranty

* It is allowed to use only protected Li-Ion batteries.

Contact us in any way convenient for you!

Armytek Optoelectronics Inc. Wholesale Department

13-85 West Wilmot St
Richmond Hill, Ontario
L4B 1K7, Canada

+1 (289) 379-9933
world@armytek.com
www.armytek.com



Set description:

