



DisplayPort Cable, 7.5m

Part No.: 41324

Description

- DisplayPort 1.1 HD 1600p compatible
- Full support for high definition video, multi-channel digital audio and DPCP
- 24K gold plated connector pins
- Supports resolutions up to 2560 x 1600, 1600p
- Supports 8 channel, uncompressed 24bit audio
- Bandwidth: 10.8Gbps total
- 10 year warranty

Technical details

This superb DisplayPort cable benefits from advanced design and construction to provide the best possible performance and reliability. Its 24K gold plated connector pins ensure superb signal integrity and corrosion resistance whilst the shielded cable design allows consistent performance, even over longer transmission distances. , it's the perfect choice for the next generation of high definition video cards and monitors.

Technical Specifications

- 10.8 Gbps forward link channel supports high resolution monitors up to 2560 x 1600 with a single cable
- 8B/10B data transmission
- Supports high definition video, multi-channel digital audio, DPCP and HDCP
- Supports color depths of 6, 8, 10, 12 and 16 bits per component
- 128-bit AES DisplayPort Content Protection (DPCP) support
- Notebook and motherboard chipsets usually have a weaker output than graphics cards
- Notebook chipsets (eg Mobile Intel 4 Series Express Chipset) may not support cable lengths over 10m
- Higher-grade graphics cards (eg NVideo FX580) also support resolutions of 2560x1600 with cable lengths up to 20m

- 10 year warranty

© LINDY 2019