

## CT590 S

CT 590 S

THE ENTRY LEVEL DUAL BANDER BECOMES EVEN MORE COMPETITIVE



### Main features

- VHF and UHF bands and channel name displayed
- Operating modes: UHF/VHF, UHF/UHF, VHF/VHF
- Output power: 5W UHF/VHF
- Up to 128 memory channels
- 50 CTCSS tones and 208 DCS codes
- 1750Hz tone for repeaters
- SOS Emergency function
- LCD display with backlight adjustable in 3 colors
- FM radio receiver (88-108MHz)
- VOX, Scan, Dual Watch functions
- Channel spacing: 25KHz/12.5KHz
- Channel or frequency mode selection
- TOT (Time out timer)
- DTMF function
- Reverse function
- Alarm function
- CTCSS and DCS codes research
- Setting and storing of channel names
- PTT-ID
- Busy Channel Lockout function (BCL)
- High/low power selection
- Frequency step: 2.5/5/6.25/10/12.5/25KHz
- Frequency offset (adjustable): 0-38.000MHz

- Repeater shift
- Squelch adjustable in 9 levels
- VOICE: vocal indication of the function selected
- Keypad lock
- Power Save
- Li-Ion 1500mAh battery pack
- 2pin Kenwood accessory jack

### Content of the packaging

- 1 CT590S transceiver with belt clip
- 1 Li-Ion battery pack 1500mAh 7.4V
- 1 fast desktop charger
- 1 wall adaptor
- Antenna