

TORCH250 USB POWER HUB + FLASHLIGHT

Stay Connected During an Outage

USB port charges phones and boosts tablets to stay connected. Long-lasting lithium battery.

Multiple Light Options for Every Situation

Use as a flashlight, floodlight or red emergency light. Save on power with bright and half-bright modes.

Built-in Charging Cable, Solar Panel, and Hand Crank

Recharge anywhere, anytime. Power for emergencies and activities.



THREE WAYS TO POWER



ANY USB PORT



BUILT-IN SOLAR



HAND CRANK

WHAT IT POWERS



HEADLAMP
2-5 RECHARGES



POV CAMERA
3 RECHARGES



PHONE
2 RECHARGES




TABLET
50% BOOST



TORCH250

USB POWER HUB + FLASHLIGHT



BUILT-IN USB PORT
Charge phones, boost tablets, stay connected



	RUN TIME		CHARGE TIME
Spot Light (low power)	15 hours	USB source	7 hours
Spot Light (high power)	7 hours	Hand crank	2.2 W (cranking at 120 RPM), 1 min. of crank=2 min light
Flood Light (low power)	48 hours	Nomad 7	7-14 hours
Flood Light (high power)	22 hours	Built-in solar	23-46 hours



TECHNICAL SPECIFICATIONS

GENERAL: Weight: 14.4 oz (408 g)
Dimensions: 10 x 3.5 x 1.75 in (25.4 x 8.9 x 4.5 cm)
LIGHT: 250 Lumens, 4,000K warm white LEDs
Spot Light: 180 Lumens
Flood Light: 70 Lumens
BATTERY: Cell Chemistry: Li-ion NMC
Cell Capacity: 16.3Wh (3.7V, 4,400mAh)
INPUT: USB Cable: 5V, up to 1A (5W max)
OUTPUT: USB Port: 5V, up to 1A (5W max), regulated
USE WITH: Goal Zero solar panels and power packs