

**Accessories
G 20/0.10A/F**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	G 20/0.10A/F
Order No.	0430300000
Version	Active components, Fuse
GTIN (EAN)	4008190077174
Qty.	10 pc(s).

Data sheet

Accessories G 20/0.10A/F

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	5 mm	Width (inches)	0.197 inch
Height	20 mm	Height (inches)	0.787 inch
Depth	5 mm	Depth (inches)	0.197 inch
Net weight	0.85 g		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Material data

Colour Light Grey

System specifications

Version Fuse accessories

Fuse cartridges

Cartridge fuse	G-Si. 5 x 20	Characteristics	quick-acting
Colour	Light Grey	Current	0.1 A
Melting integral	0.001 A ² s	Power output (@ 1.5 In)	0.8 W
Rated breaking capacity	1.5 kA	Version	Fuse accessories
Voltage drop	2600 mV		

Rating data

Rated voltage 250 V Rated current 0.1 A

Classifications

ETIM 3.0	EC000035	ETIM 4.0	EC000035
ETIM 5.0	EC000035	ETIM 6.0	EC000035
UNSPSC	30-21-18-14	eClass 5.1	27-14-20-07
eClass 6.2	27-14-20-07	eClass 7.1	27-14-20-90
eClass 8.1	27-14-20-90	eClass 9.0	27-14-20-01
eClass 9.1	27-14-20-01		

Approvals

ROHS Conform

Downloads

Brochure/Catalogue [CAT 1 TERM 16/17 EN](#)