

**BG GH CUTOUT PT6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The FieldPower® housings are highly robust and meet the highest UL flammability class 5 VA.

- The "TS 35 PT6" mounting rail module and PT6 contact unit are easy to snap on.
- Hinged seals allow pre-assembled plug cables to also be used.
- The high cover versions enable the device to be installed.

For cable seals consult accessories.

**General ordering data**

Type	BG GH CUTOUT PT6
Order No.	<a href="#">1272210000</a>
GTIN (EAN)	4032248113743
Qty.	1 pc(s).

**BG GH CUTOUT PT6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	303 g
------------	-------

**Temperatures**

Operating temperature, max.	55 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...55 °C	Storage temperature	-40 °C...85 °C

**General specifications**

Halogen	No	Insulating material	Polycarbonate, GF 10
Protection degree	IP65, in closed state	Silicone	Yes
Colour	black	UL 94 flammability rating	5VA
Torque for lid screws	2 Nm	Enclosure attachment	Fixing lugs

**Classifications**

ETIM 5.0	EC000775	ETIM 6.0	EC000261
eClass 6.2	27-14-24-14	eClass 7.1	27-14-24-14
eClass 8.1	27-14-24-14	eClass 9.0	27-18-01-90
eClass 9.1	27-18-92-90		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">FieldPower</a>
---	----------------------------

**BG GH CUTOUT PT6**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

