

**Accessories**  
**G 20/0.63A/F****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image**

Similar to illustration

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	G 20/0.63A/F
Order No.	<a href="#">0439000000</a>
Version	Active components, Fuse
GTIN (EAN)	4008190131210
Qty.	10 pc(s).

## Data sheet

### Accessories G 20/0.63A/F

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	5 mm	Width (inches)	0.197 inch
Height	20 mm	Height (inches)	0.787 inch
Depth	5 mm	Depth (inches)	0.197 inch
Net weight	1.1 g		

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Material data

Colour Light Grey

### System specifications

Version Fuse accessories

### Fuse cartridges

Cartridge fuse	G-Si. 5 x 20	Characteristics	quick-acting
Colour	Light Grey	Current	0.63 A
Melting integral	0.31 A <sup>2</sup> s	Power output (@ 1.5 In)	1.1 W
Rated breaking capacity	1.5 kA	Version	Fuse accessories
Voltage drop	550 mV		

### Rating data

Rated voltage	250 V	Rated current	0.63 A
---------------	-------	---------------	--------

### Classifications

ETIM 3.0	EC000035	ETIM 4.0	EC000035
ETIM 5.0	EC000035	ETIM 6.0	EC000035
UNSPSC	30-21-18-14	eClass 5.1	27-14-20-07
eClass 6.2	27-14-20-07	eClass 7.1	27-14-20-90
eClass 8.1	27-14-20-90	eClass 9.0	27-14-20-01
eClass 9.1	27-14-20-01		

### Approvals

ROHS Conform

### Downloads

Brochure/Catalogue [CAT 1 TERM 16/17 EN](#)