

Accessories
GZ 10.0A/F

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	GZ 10.0A/F
Order No.	1460640000
Version	Accessories, Fuse, 10 A
GTIN (EAN)	4050118266801
Qty.	10 pc(s).

Accessories

GZ 10.0A/F

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	6.3 mm	Width (inches)	0.248 inch
Height	32 mm	Height (inches)	1.26 inch
Depth	6.3 mm	Depth (inches)	0.248 inch
Net weight	2.476 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Colour	Light Grey
--------	------------

System specifications

Version	Fuse accessories
---------	------------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

Fuse cartridges

Cartridge fuse	G-Si. 6.3 x 32	Characteristics	quick-acting
Colour	Light Grey	Current	10 A
Melting integral	240 A ² s	Power output (@ 1.5 In)	4 W
Rated breaking capacity	1.5 kA	Version	Fuse accessories
Voltage drop	150 mV		

Rating data

Rated voltage	500 V	Rated current	10 A
---------------	-------	---------------	------

Classifications

ETIM 3.0	EC000035	ETIM 6.0	EC000035
UNSPSC	30-21-18-14	eClass 5.1	27-14-20-07
eClass 6.2	27-14-20-07	eClass 7.1	27-14-20-90
eClass 8.1	27-14-20-01	eClass 9.0	27-14-20-01
eClass 9.1	27-14-20-01		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
--------------------	-------------------------------------