


WIRELESS GATEWAYS AND REPEATERS

Gateway RF compatible to TP paladin 673 520 rf



Overview

- Gateway / media coupler KNX-RF compatible products to KNX-TP
- 16 RF-channels
- RF-repeater function included
- Compact housing
- Flush-mounted fitting
- Protection class IP 20
- KNX-RF compatible

Order numbers

■ **paladin**

673 520 rf

Gateway RF compatible products to KNX-TP

WIRELESS GATEWAYS AND REPEATERS

Gateway RF compatible to TP paladin 673 520 rf

Technical data

Supply voltage	21-32 V DC via KNX-Bus
Bus current	<10 mA
RF Transmission type	Codified transmission in 868,4 MHz with ERP>8 mW and a coverage of 100 m (in the free field)
RF Channels	16
TP Group addresses	250
TP Connections	250
ETS Version	ETS 4 or higher
Communication	Bi-directional
Permitted ambient temperature	-5°C...+45°C
Dimensions	49 x 48 x 18 mm
Mounting	Recessed ceiling mounting
Connection type	KNX-Bus terminal
Protection class	IP 20

Rights to technical amendments reserved / Technische Änderungen vorbehalten
 Droits de modifications techniques réservés / Suscettibile di errori e modifiche

