

SWITCHING ACTUATOR

paladin 683 730 rfs



Overview

- Switching actuator 1-channel
- Functions: Switching (on / off), Timer, Staircase lighting timer with advanced warning function
- Breaking capacity: 250 V / 16 A
- RF-repeater function included
- Compact housing
- Flush-mounted fitting
- Protection class IP 20
- KNX-RF 1.R S-Mode

Order numbers

■ **paladin**

683 730 rfs 1-channel

availability: approx. by
the end of Q3/2018

Technische Änderungen vorbehalten.

SWITCHING ACTUATOR

paladin 683 730 rfs

Technical data

Power supply	110-230 V 50 Hz
Switching capacity	μ 16A / 250V LED lamps 400W Incandescence / 230V Halogens 3000W Fluorescence 1300 W (130μF)
KNX Medium	KNX RF 1.R
Radio frequency	868,3MHz
Transmission power	< 10dBm
Range (max.)	In free field: 100m / Indoors: ~30m
Number of outputs	1
Working modes	Switch Timer KNX-RF signals Repeater
Application Software	ETS5
Commissioning mode	System-Mode (S-Mode)
Dimensions	46 x 46 x 30mm
Mounting	Flush-mounting
Operation temperature range	-10°C ... +45°C
Degree of protection	IP20

Technische Änderungen vorbehalten.

