


DLH DQ 6.10 H55 L260 STTZN (202 040)



Figure without obligation



Type	DLH DQ 6.10 H55 L260 STTZN
Part No.	202 040
Material of roof conductor holder	St/tZn
Height of brace (h1)	55 mm
Length of brace (l1 / t1)	260 / 2 mm
Material of conductor holder	St/tZn
Conductor holder support Rd	6-10 mm
Type of conductor holder	DEHNquick
Conductor leading	fixed
Type of roofing	tiled, slated, roofing felt
Type of brace	straight
Fixing possibility	nailing, underlaying
Bore Ø	8.4 mm
Weight	170 g
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364019935
PU	50 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.