




## KS 8.10 8.10 FL30 STTZN (318 251)



Figure without obligation



Type	KS 8.10 8.10 FL30 STTZN
Part No.	318 251
Material of clamp	St/tZn
Clamping range Rd / Rd	8-10 / 8-10 mm
Clamping range Rd / FI	8-10 / 30 mm
Clamping range FI / FI	30 / 30 mm
Screw	● M8 x 25 mm
Material of screw / nut	St/tZn
Dimension	60 x 60 x 3 mm
Standard	EN 62561-1
Short-circuit current (50 Hz) (1 s; ≤ 300 °C)	14 kA
Zinc coating acc. EN 1461	≥ 70 μm
Weight	241 g
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364046559
PU	25 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.