


LH DG 8 H20 HS5X50 KD8 V2A GR (207 109)



Figure without obligation



| Type | LH DG 8 H20 HS5X50 KD8 V2A GR |
|---|-------------------------------|
| Part No. | 207 109 |
| Type of conductor holder | DEHNgrip |
| Height of conductor holder | 20 mm |
| Bore of conductor holder | Ø7.8 mm |
| Material of conductor holder | StSt |
| Conductor holder support Rd | 8 mm |
| Conductor leading | loose |
| Screw | ⌈ 5 x 50 mm |
| Plastic dowel | Ø8 x 40 mm |
| Cover plate | yes |
| Standard | EN 62561-4 |
| Weight | 27 g |
| Customs tariff number (Comb. Nomenclature EU) | 85389099 |
| GTIN | 4013364085800 |
| PU | 50 pc(s) |

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.