



KS 8.10 FL30 V4A (318 209)





Figure without obligation



Type	KS 8.10 FL30 V4A
Part No.	318 209
Material of clamp	StSt (V4A)
Clamping range Rd / FI	8-10 / 30 mm
Clamping range FI / FI	30 / 30 mm
Clamping range (stranded / cable)	50-70 mm ²
Screw	☛ M8 x 25 mm
Material of screw / nut	StSt (V4A)
Material No.	1.4571 / 1.4404 / 1.4401
ASTM / AISI:	316Ti / 316L / 316
Dimension	60 x 60 x 3 mm
Standard	EN 62561-1
Short-circuit current (50 Hz) (1 s; ≤ 300 °C)	7.4 kA
Weight	245 g
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364035973
PU	25 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.