




AK ZS 8.10 FL30 GBM10X60 V4A (478 129)



Figure without obligation



Type	AK ZS 8.10 FL30 GBM10X60 V4A
Part No.	478 129
Material of clamp	StSt (V4A)
Clamping range Rd / FI	8-10 / 30 mm
Material of bolt	StSt (V4A)
Screw	☛ M10 x 60 / M8 x 16 mm
Material of screw / nut	StSt (V4A)
Material No.	1.4571 / 1.4404 / 1.4401
Dimension	58 x 30 x 2.5 mm
Standard	EN 62561-1
Short-circuit current (50 Hz) (1 s; ≤ 300 °C)	2.7 kA
Weight	140 g
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364118508
PU	10 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.