




BRS 16.89 AK1X10 2X6.8 V2A (540 103)



Figure without obligation



Type	BRS 16.89 AK1X10 2X6.8 V2A
Part No.	540 103
Material	StSt
Clamping range pipe Ø	16-89 mm (³ / ₄ -3")
Screw	☒ M8 x 20 mm
Material of screw	StSt
Dimension of strap (l1 x w x d)	330 x 25 x 0.3 mm
Connection Rd	1-2 conductors Rd Ø6-8 mm / 1x Ø10 mm
Connection (solid / stranded)	4-50 mm ²
Standard	EN 62561-1
Weight	120 g
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364101302
PU	10 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.