


DC BK 6 RD10 STBLANK (308 130)



Figure without obligation



- Compact, light and resource-saving
- Quick and toolless
- Efficient and time-saving

| Type | DC BK 6 RD10 STBLANK |
|---|----------------------|
| Part No. | 308 130 |
| Material | St/bare |
| Clamping range Rd* / Rd | 6-7 / 10 mm |
| Material thickness (t1) | 1 mm |
| Short-circuit current (50 Hz) (1 s; ≤ 300 °C) | 2.5 kA |
| Standard | EN 62561-1 |
| Weight | 18 g |
| Customs tariff number (Comb. Nomenclature EU) | 85389099 |
| GTIN | 4013364288942 |
| PU | 50 pc(s) |

* Nominal diameter d_s of the reinforcement

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.