




DRK ZS 7.10 W13.25 CU (338 007)



Figure without obligation



Type	DRK ZS 7.10 W13.25 CU
Part No.	338 007
Clamping range of bead	13-25 mm
Material of clamp	Cu
Clamping range Rd	7-10 mm
Material of cleat	Cu
Width / material thickness	40 / 3 mm
Screw	☛ M6 x 16 / M6 x 10 mm
Material of screw	StSt
Standard	EN 62561-1
Weight	190 g
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364024854
PU	25 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.