




PV 7.10 FRM10X35 V4A (306 029)



Figure without obligation



Type	PV 7.10 FRM10X35 V4A
Part No.	306 029
Material of clamp	StSt (V4A)
Clamping range Rd / Rd	7-10 mm
Screw	⬆ M10 x 35 mm
Material of screw / nut	StSt (V4A)
Material No.	1.4571 / 1.4404 / 1.4401
ASTM / AISI:	316Ti / 316L / 316
Standard	EN 62561-1
Type	also for underground application
Short-circuit current (50 Hz) (1 s; ≤ 300 °C)	2.9 kA
Material thickness	3 mm
Weight	120 g
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364129467
PU	50 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.