




## RRS V 60.150 B10.5 V2A (423 029)



Figure without obligation



Type	RRS V 60.150 B10.5 V2A
Part No.	423 029
Material	StSt
Clamping range pipe Ø (d1)	60-150 mm
Length (l1)	494 mm
Bore Ø	10.5 mm
Screw	☿ M8 x 25 mm
Material of screw / nut	StSt
Standard	EN 62561-1
Weight	151 g
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364054318
PU	50 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.