


RE 25 1500 V4A (649 150)



Figure without obligation



Type	RE 25 1500 V4A
Part No.	649 150
Material	StSt (V4A)
Material No.	1.4571 / 1.4404 / 1.4401
ASTM / AISI:	316Ti / 316L / 316
Rod length	1500 mm
Diameter Ø	25 mm
Standard	EN 62561-2
Wall thickness	2 mm
Cross section	145 mm ²
Weight	1.7 kg
Tenon	21 mm
Tensile strength	500-700 N/mm ²
Static tensile strength (vertical tension)	approx. 40000 N
Conductivity	≥ 1.25 m / Ohm mm ²
Specific resistance	≤ 0.80 Ohm mm ² / m
Weight	1,71 kg
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364126350
PU	6 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.