

KERN CP200-3P9

Single-point load cells made of stainless steel with IP69K protection



Measuring system

Combined Error:	0,023 %
Load cell connection:	4-Leiter
Nominal sensitivity:	2
OIML class:	C3
Resolution Load cell â Verifiable:	3000 e
Weighing capacity [Max]:	200 kg
Y value:	10000

Environmental conditions

Maximum operating temperature:	65 °C
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-35 °C
Minimum operating temperature:	-10 °C

Category

Brand:	Sauter
--------	--------

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	280 x 175 x 125 mm
Gross weight:	3,302 kg
Net weight:	2,767 kg
Shipping method:	Parcel service

Construction

Cable length:	3 m
Dimensions (WxDxH):	174 x 45 x 64 mm
Dimensions of weighing plate (WxDxH):	800 x 800 x 0 mm

Piktogramme

STANDARD

