

Y80



Large HD+ widescreen



Powerful performance



Dual camera
with bokeh mode



Big battery



Big display. Big battery.

Entertain yourself on a large HD+ widescreen for a full day of top multimedia experience. The Y80's octa-core processor and big battery won't let you down. Impress with cool shots thanks to the AI powered dual camera.

Available colors: ● Gradient dark blue ● Gradient bleen ● Gold

CUSTOMISED ACCESSORIES

- **Easy Folio** with a translucent flip cover to keep track of your notifications
- Clear and **Flexible Case** to safeguard your phone
- Ultra-resistant **Printed Tempered Glass** for full screen protection

Main features	
Network	4G LTE B1 (2100)/ B3 (1800)/ B5 (850)/ B7 (2600)/ B8 (900)/ B20 (800) H+/3G+/3G HSPA+ 850/ 900/ 1900/ 2100 MHz GSM/GPRS/EDGE 850/900/1800/1900 MHz
Data Segment	FDD-LTE Category 4 DL 150 Mbps, UL 50 Mbps
Operating System	Android™ 9.0 (Pie)
Processor	Unisoc SC9863A, Octa-Core 1.6GHz
GPU	IMG 8322
Design	Touch screen
SIM CARD	1 Micro SIM + 1 Nano SIM
Available colors	Gradient Dark Blue (Anthracite Blue), Gradient Bleen (Bleen), Gold
Size	160 x 76.5 x 8.55 mm
Weight	185g
Battery	4000 mAh Li-Po
Stand-by time	Up to 286h
Talk time	Up to 38h (2G), 22h (3G)
ROM	16 GB
RAM	2 GB
External memory	Micro SD up to 128 GB
Accelerometer	Yes
Magnetic sensor	Yes
Proximity sensor	Yes
Light sensor	Yes
SAR value	Head: 0.49W/kg, Body: 1.35W/kg
Display	
Size	5.99
Type	IPS technology, 2.5D glass
Color	16 million
Display resolution	HD+ (1440x720 pixels), pixel density: 269 PPI
Multitouch	Yes
Connectivity	
Wi-Fi	802.11 b/g/n
Tethering	USB, Bluetooth, Access Point Wi-Fi
Bluetooth®	4.2
USB™ OTG	Yes
PORT USB™	2.0
PC synchronization	Yes
Audio jack	3.5mm jack
Photo & Video	
Main camera	Dual 13+2 Megapixels
Option	Face Beauty, Night Mode, HDR, Live Filter, Time-Lapse, Live Portrait (front), Live Artistic Blur (rear), AI mode, Professional mode
Flash	LED
Front Camera	5 Megapixels

Digital Zoom	4x
Auto Focus	Yes
Image editor	Yes
White Balance	Auto, Incandescent, Daylight, Fluorescent, Cloudy
Video recorder	1080p@30fps
Multimedia and Entertainment	
Supported sound formats	MP3, AMR, WAV, AAC
Supported image formats	JPEG, GIF, PNG, BMP
Supported video formats	AVI, MP4, 3GP, H.264
GPS system	
GPS	Yes
A-GPS	Yes
Customization	
Languages	English, French, Italian, German, Dutch, Spanish, Portuguese, Russian, Czech, Polish, Finnish, Hungarian, Arabic, Urdu, Persian, Danish, Norwegian, Swedish, Thai, Indonesian, Vietnamese, Turkish, Cyrillic Serbian, Latin Serbian, Slovenian, Macedonian, Croatian, Catalan, Basque, Romanian, Polish, Slovak, Ukrainian, Greek
Wiko features	Face Unlock, Wiko Launcher, Smart Assist, One-handed mode, Smart actions, Smart screenshot
Google™ Mobile Service	
Applications	Yes
In the box	
	AC adapter Headset Micro USB Cable Wiko mobile phone Quick Start Guide Safety Book
Specifications, features and appearance of the product may be altered without notification. Access to Google™ applications can differ depending on your country.	

