

KERN CT1000-3P1

Measuring cells made from stainless steel



Measuring system

Combined Error:	0,023 %
Load cell connection:	4-Leiter
Nominal sensitivity:	3
OIML class:	C3
Resolution Load cell â Verifiable:	3000 e
Weighing capacity [Max]:	1 t
Y value:	10000

Environmental conditions

Maximum operating temperature:	65 °C
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-35 °C
Minimum operating temperature:	-10 °C

Category

Brand:	Sauter
--------	--------

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	225 x 115 x 45 mm
Gross weight:	1,010 kg
Net weight:	908 g
Shipping method:	Parcel service

Construction

Cable length:	4 m
Dimensions (WxDxH):	130 x 34 x 31,8 mm

Piktogramme

STANDARD

