

Item no.: 2108927 / 2108928 / 2108938 / 2108925

Data Sheet

VGA3+9 terminal connector modular



T1904C096 - Male connector with jackscrew nut connection



T1904C097 - Female connector with jackscrew nut connection



T1904C098 - Male connector with locking screw connection



T1904C099 - Female connector with locking screw connection

Included accessories
 1x Screw driver
 1x Cable strain Relief
 2x Fastening screw

Housing dimension



Material:

Housing: PP

Connector insulator: PBT+30%GF (UL94V-0)

Contact: Brass

Contact plated: Nickel

Connector shell plated: Cu60µ/Ni100-120µ

Technical:


Contact current rating: 5A max.

Insulation resistance: 1000MΩ min. at 500V/DC


Dielectric withstanding voltage: 500V/AC(R.M.S)/1 minute

Operation temperature: -20 ~85°C

Male



Female



- 1 RED video
- 2 GREEN video
- 3 BLUE video
- 4 ID2/RES
- 5 GND
- 6 RED_RTN
- 7 GREEN_RTN
- 8 BLUE_RTN
- 9 KEY/PWR
- 10 GND
- 11 ID0/RES
- 12 ID1/SDA
- 13 HSync
- 14 VSync
- 15 ID3/SCL