

KERN HDB10K10N

Praktisch, preiswert und stets griffbereit

KERN[®]



Functions

Data hold function: yes

Environmental conditions

Maximum humidity: 90 %

Maximum operating temperature: 35 °C

Minimum ambient temperature: 5 °C

Power supply

Operating time: 180 h

Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128H

Category

Brand: KERN

Category: Balances

Product Group: Hanging scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 70 x 150 x 225 mm

Gross weight: 400 g

Net weight: 200 g

Shipping method: Parcel service

Construction

Casing material: Plastic

Dimensions housing (WxDxH): 70 x 25 x 105 mm

Overall dimensions mounted (WxDxH): 195 x 70 x 25 mm

Measuring system

Adjustment options: External calibration

Linearity: 30 g

Precision (of [Max]): 0,005

Readout [d]: 10 g

Recommended adjusting weight: 10 kg (M1)

Reproducibility: 10 g

Resolution: 1000

Stabilisation time: 2 s

Warm up time: 10 min

Weighing range [Max]: 10 kg

Weighing system: Strain gauge

Weighing units: kg lb N

Display

Display digit height: 1,200 cm