

JOY-VIEW 15

MOBILE IPS MONITOR WITH RAZOR-SHARP FULL HD RESOLUTION FOR A FIRST-CLASS VIEWING EXPERIENCE

JOY-IT

SPECIAL FEATURES

- ✓ Portable IPS display with Full HD resolution
- ✓ 10-point multi-touchscreen
- ✓ Ultra-slim design with integrated stereo speakers
- ✓ Robust aluminum housing
- ✓ Ideal for working and traveling
- ✓ Single-cable solution: Simple setup of compatible devices via a single USB-C port
- ✓ Additional audio socket for connecting headphones or speakers



The Joy-View is your perfect companion for any use - whether at work or on the move. With its portable IPS display and razor-sharp Full HD resolution, it offers you a brilliant image experience that displays your content in vivid colors and impressive clarity. The 10-point multi-touch screen ensures intuitive operation and opens up a whole new way of interacting - ideal for creative work.

Thanks to its ultra-slim design with integrated stereo sound, the Joy-View blends seamlessly into any environment. Its robust aluminum housing makes it not only stylish, but also durable for use on the go. With the single-cable solution via USB-C, you can connect your notebook, smartphone or other compatible devices simply and easily - power supply and image transmission run via a single cable.

In addition, the mini HDMI port offers further flexibility to connect your games console or other devices.

The included smart case reliably protects the Joy-View during transportation and also serves as a stable stand so that your display is always safe and ready for use. The additional audio socket also allows you to connect headphones or external speakers to create the perfect audiovisual experience.

Whether as a second screen for your PC or as a mobile display, the Joy-View turns your smartphone into a powerful laptop in no time at all - without expensive additional devices. With its flexibility and first-class features, the Joy-View offers an incomparable user experience. Stay mobile and productive at all times, without compromise.

MAIN FEATURES

Resolution	1920 x 1080
Screen size	15.6" (39.62 cm)
Inputs	Mini HDMI, Type-C, power input
Outputs	3.5mm jack plug
Power supply	USB Type-C PD 5 - 20 V (single-cable solution), USB Type-C (two-cable solution)
Energy efficiency class	Class A
Housing	Aluminum alloy
Smart Case	Smart case included in the scope of delivery serves both as protection and as a folding stand

DISPLAY FEATURES

Refresh rate	60 Hz
Contrast	800:1
Brightness	300 nit
Screen type	TFT IPS LCD
Backlight	LED backlight
Color space	16.7 million colors, NTSC 72%, sRGB up to 100%
Aspect ratio	16:9
Point of view	178°
Loudspeaker	Stereo speaker 8Ω2W

ADDITIONAL INFORMATION

Operating temperature	0 - 50 °C
Item number	JT-View15
Scope of delivery	Joy-View display, smart case, 1.5 m HDMI to miniHDMI cable, 1 m USB-A to USB-C cable, 1 m USB Type-C to USB Type-C cable, power adapter, HDMI to miniHDMI adapter, cleaning cloth
EAN	4250236818894
Customs tariff number	8473302000

