


JAVELOT PRO

EXTEND YOUR LIMITS

MAX OUTPUT	MAX RUNTIME	MAX THROW
		
2,100 lumens	8 days	1080 meters



MARKET APPLICATIONS

Hunting
Search and Rescue

DESCRIPTION

The Javelot Pro is a dual-switch LED flashlight succeeding the M3XS-UT that delivers a beam distance of more than 1000 meters. The flashlight has an integrated 25Wh (two 3500mAh 18650 lithium batteries) rechargeable battery pack. The Javelot Pro delivers a maximum output of 2,100 lumens and a beam distance of 1080 meters. It adopts the OLIGHT signature versatile tail switch, functioning as a tail switch, charging port and connection port for a magnetic remote pressure switch. The Javelot Pro can also be controlled from the side switch. With high performance and easy operation, the Javelot Pro is suitable for a multitude of outdoor activities. With a bezel diameter of 63mm, a high capacity battery pack, convenient charging system and easy operation, the Javelot Pro is the best illumination tool for hunting or search and rescue.



FEATURES

- **Powerful performance:** Powered by a rechargeable battery pack integrated into the handle (two 3500mAh 18650 lithium batteries), delivering a maximum output of 2,100 lumens and a beam distance of 1080 meters.
- **Two versatile switches:** The tail switch delivers 2,100 lumens high mode and 15 lumens low mode. The side switch can turn the light on or off and cycles through the following modes: 2,100 lumens, 600 lumens, 150 lumens and 15 lumens.
- **LED indicator centered in the side switch:** When the indicator lights up green, there is more than 75% of battery left; the orange indicator represents 30%-75% of battery power; when the battery power is less than 30%, the red indicator lights up; when the battery power is less than 10%, the red indicator will blink.
- **Tower-shaped tube body** provides comfort and a firm grip for superior performance.
- **Magnetic tail cap:** Functioning as a charging port or magnetic pressure switch mount.

OUTPUT

FL1 STANDARD	Mode 1	Mode 2	Mode 3	Mode 4
	2,100 ± 1000 lumens	600 lumens	150 lumens	15 lumens
	10+130 minutes	5 hours	23 hours	8 days
	1080 meters	540 meters	270 meters	90 meters
	291,600 cd			

LIGHT SOURCE

Cree XHP35 HI NW

DIMENSIONS

Length: 9.72in/247mm
Head Diameter: 2.48in/63mm
Body Diameter: 1.02in/26mm

WEIGHT

13.4oz/380g (including battery pack)

WATERPROOF IPX8



DROP TEST



COMPLIANCE



BODY MATERIAL

AL6061-T6 Aluminum Alloy

BATTERY SOURCE

Integrated battery pack

The above data are test results retrieved according to ANSI NEMA FL 1-2009 standards.

IN THE BOX

Flashlight x 1
Magnetic USB charging cable MCC5V x 1
Holster (in the package) x 1
User manual x 1

X-WM03 (OPTIONAL)



Adjustable ring



Up to 180°

Three magnets

DIMENSIONS

Length: 1.78in/45mm
Width: 1.97in/50mm
Height: 2.37in/60mm

WEIGHT

4.3oz/122g

BODY MATERIAL

Aluminum Alloy

FITS

OLIGHT M20 SERIES, M22, M23, M2X,
M3XS, WARRIOR X, JAVELOT PRO

DESCRIPTION

X-WM03 is the third generation of OLIGHT magnetic mount, suitable for flashlights with the body diameter between 23mm and 26mm. It comes with three magnets while maintaining the same size and weight as X-WM02. Its doubled magnetic adsorption force makes it a perfect choice for hunting.

FEATURES

- Flip angle of the mount clamp is improved to reach 180°, making flashlight installation much easier.
- Accepts 23mm-26mm diameter sized flashlights.
- With three strong N52 rectangular magnets(the included angle between any two magnets is 135°), the magnetic adsorption force is doubled than that of the previous two magnets.
- Rotate the adjustable ring to make the middle magnet at proper height to fit different diameter of body.