

DENVER SCO-65220

- Electric Scooter with aluminum frame & 300W electric motor
- LED light + reflectors in front, sides & back of the scooter
- Bell on the steer
- Engine is in the frontwheel
- Front suspension for comfortable ride
- Maximum speed up to 20 km/h
- Supports persons up to 100 kg
- Built-in rechargeable battery (14 x 18650 battery cells - 25.2V - 4000mAh in total)
- Charge time 2-3 hours
- Driving range charge: 12 km
- Foldable for easy carrying
- Anti slip material for standing platform
- Electric brake on front wheel, and manual foot brake made of metal on back
- Front fender for front wheel
- Lightweight: 8,9 Kg
- 6,5" Wheels in durable rubber
- Including multifunctional display (speed, distance, battery charge indicator, gear indicator)
- Compliant for public ride & use in many countries, check your local rules to see if your country is included

Please notice:

Speed and range may differ based on rider weight, terrain, temperature, and driving style





Always make sure to wear safety gear

Only for use in dry weather

Important maintenance information

Please find PDF file describing how to do maintenance on your scooter [here](#) <--



-  Highlights
300W engine, Max. speed up to 20km/h, range up to 12 km, foldable, 6.5" wheels, light weight, light in front & back, reflectors in front & back, bell
-  Power
230V charger included
-  Battery
Built-in rechargeable battery (14 x 18650 battery cells - 25.2V - 4000mAh in total)
-  Materials
Aluminium frame, rubber wheels/handles

Shipping information

Unit size: 47(w) x 98(d) x 110(h) cm

Unit weight: 12,83

1 Pcs./export carton

288 Pcs./20' container

700 Pcs./40' HQ container

Barcode: 5706751044946