



Part No	90NB0MS2-M02230
Model Name	F409FA-EK160T
EAN Code	4718017466530
UPC Code	192876466537
LCD Cover Color & Decoration	Slate Gray
Top Case Color & Decoration	Slate Gray
On board processor	Intel® Core™ i5-8265U Processor 1.6 GHz (6M Cache, up to 3.9 GHz)
Operating System	Windows 10 (64bit)
Office	Includes 1 month Trial for New Microsoft Office 365 Customers
Display	14.0'//200nits//FHD 1920x1080 16:9//Anti-Glare//NTSC: 45%
Number Pad	N/A
ScreenPad™	N/A
Chipset	N/A
Memory Slot	1x
Total System Memory	4GB on board + DRAM DDR4 4GB
On board memory	4GB on board
Memory Max.	16G
DIMM Memory	DRAM DDR4 4GB
Storage	PCIEG3x2 NVME 256GB M.2 SSD
Expansion Slot	DDR4*1 M.2 2280 PCIE G3X4 *1 M.2 2280 SATA3 *1 STD 2.5" SATA HDD *1
EMMC/ISSD	N/A
External video display modes	HDMI 1.4
Discrete/Share	Share
IGPU	Intel UHD Graphics 620
Video memory	N/A
Video Camera	VGA Web Camera (Fixed type)
FingerPrint	N/A
On board Wireless	N/A
Wireless(Module)	Wi-Fi 5(802.11ac)+Bluetooth 4.1 (Dual band) 1*1
LAN	N/A
Card Reader	Type: Micro SD Spec: SDXC
USB Port	2x USB 2.0 1x USB3.1 Type A (Gen1) 1x USB3.1 Type C (Gen 1)

Interface	1x Headphone-out & Audio-in Combo Jack 1x HDMI 1x USB3.1-Type C(Gen1)
Audio	Built-in speaker Built-in microphone Audio by ICEpower®
Weight (Kg)	1.40 KG (Without Battery) 1.60 KG (with 2 cell battery)
Dimension (cm)	32.5(W) x 21.6(D) x 2.31 ~ 2.31 (H) cm
AC Adapter	ø4.0 45W AC Adapter Output: 19V DC, 2.37A, 45W , Input: 100~240V AC 50/60Hz universal
Battery	32WHrs, 2S1P, 2-cell Li-ion
Replaceable Battery	No
Keyboard type	Chiclet Keyboard
Software	ICESound McAfee Internet Security(Trial version)
Security	TPM (Firmware TPM)
Supplied Accessories	

