



Surftab Y10

Hardware

Processor (CPU)	MT8765 processor, 1.3 GHz, 64-Bit ArmV8 Cortex-A53 Quad Core
Operating system	Android™ 9 Pie
RAM	2 GB
Internal storage	32 GB ²
Graphic Unit (GPU)	Mali-T720 MP2
Display size	25.7 cm (10.1")
Display type	5-point capacitive multi-touch HD IPS display
Screen resolution	1280 x 800 pixel
Aspect ratio	16:10
Camera	Front: 0.3 MP, Rear: 2 MP
Speaker	Stereo
Microphone	yes
Interface	1 x Micro-USB 2.0 (with host function), memory card reader, audio out/mic in (3.5 mm), SIM card slot LTE
Network	WiFi, Bluetooth 4.0
Frequencies	WiFi 802.11a/b/g/n:2.4 GHz/5 GHz
Memory extension	microSD(HC/XC) up to 256 GB
Dimensions	approx. 243.8 mm x 162.3 mm x 9.2 mm
Weight	approx. 477 g
Housing material	plastic
Color	Black

Surftab Y10

Record and playback

Playable video formats	MPEG-4.10 H.264/AVC (MP@L4.1, HP@L4.0), MPEG-4.2 SP/ASP (e.g. Xvid)
Video container formats	AVI, MKV, MOV
Gaming	3D games, Classic games
Supported picture formats	JPEG, PNG, GIF, BMP
Playable audio formats	MP3, WAV, OGG, FLAC, AAC

Battery and power supply

Type of battery	Lithium polymer
Capacity of battery	3.7 V / 5000 mAh / 18.500 Wh
Charge by	Micro-USB
Power supply	230 V (110 V - 240 V)

Other characteristics

More	GPS, G-sensor
Languages	Multilanguage support via Android™ OS 9
Package contents	Surftab Y10 LTE, USB host adapter cable, OTG cable, power adapter (100 V - 240 V), cleaning cloth, quick guide, important safety and legal information

Operation and storage

Temperatures	5° C to 30° C
Relative humidity	30 % to 70 %

* 1 GB = 1 000 000 000 Bytes.

Memory card not included in the delivery.
The battery in this product cannot be easily replaced by users themselves.
We reserve the right to make changes and corrections.