



## MiniPC WBX5005

### Hardware

Processor (CPU)	Intel® Broadwell-U i3-5005U (up to 2.0 GHz) dual core
Operating system	Windows 10 Home in S mode
RAM	4 GB
Internal storage	128 GB* SSD
Graphic Unit (GPU)	Intel® HD Graphics 5500
Interface	2 x HDMI® 1.4, 2 x USB-A 2.0, 2 x USB-A 3.1 Gen 1, 1 x LAN RJ45, USB 3.1 Gen.1 Type-C (data only), audio out/mic in (3.5 mm), memory card reader, WiFi, Bluetooth 4.2, DC IN
Memory extension	microSD(HC/XC) up to 256 GB, M.2 SSD extension
Dimensions	approx. 112 mm x 124 mm x 44.5 mm
Weight	approx. 335 g
Housing material	plastic
Color	Black, Grey

### Internet connection

WiFi	802.11 a/b/g/n/ac 2.4 & 5GHz
------	------------------------------

### Record and playback

Video playback	Full HD (1080p)
Playable video formats	DivX, MPEG-4.10 H.264/AVC (MP@L4.1, HP@L4.0), MPEG-4.2 SP/ASP (e.g. Xvid)
Video container formats	AVI, MP4, WMV
Supported picture formats	BMP, GIF, JPEG, PNG
Playable audio formats	AAC, MP3, PCM, WAV, WMA

## MiniPC WBX5005

### Other characteristics

Power supply

power adapter

Package contents

MiniPC WBX5005, power adapter (100 V - 240 V), quick guide, important safety and legal information, VESA adapter (optional)

\* 1 GB = 1 000 000 000 Bytes.

Memory card not included in the delivery.  
We reserve the right to make changes and corrections.