

VAIO® SX14

CPU	Intel® Core™ i7-8565U processor (8M Cache, up to 4.60 GHz)
OS	Windows 10 Professional
Display	14.0" anti-glare UHD IPS display (3840x2160), brightness 450 nits
GPU	Intel® UHD Graphics 620
RAM	16 GB LPDDR3
SSD	512 GB PCIe NVMe
Network	WiFi IEEE 802.11a/b/g/n/ac: 2.4 GHz/5 GHz Gigabit-LAN Bluetooth® 4.1 Mobile data (microSIM): (3G Band: 1, 2, 4, 5, 6, 8, 19) (4G Band: 1, 2, 3, 4, 5, 7, 8, 12, 13, 17, 18, 19, 20, 21, 25, 26, 28, 29, 30, 38, 39, 40, 41, 66)
I/O	USB Type-C 3.1 Gen.2 USB Type-A 3.1 Gen.2 2x USB Type-A 3.1 Gen 1 HDMI VGA LAN RJ45 Audio out/mic in 3.5mm SD cardreader (SDHC/SDXC) up to 512 GB
Camera	Front: 0.92 MP
Misc	GPS
Security	TPM 2.0, fingerprint
Size	320.4 x 222.7 x 17.9 mm
Weight	999 g
Material	Carbon fiber, aluminium
Color	Black, silver, brown
Battery Runtime**	8.5 h
Warranty	24 months manufacturer warranty incl. pick-up and return service

* depending on model

** Runtime based on laboratory tests. Real world runtime can vary based on specifications and usage.

The battery in this product cannot be easily replaced by users themselves.
We reserve the right to make changes and corrections.