



VAIO® A12

CPU	Intel® Core™ i7-8500Y processor (4M Cache, up to 4.20 GHz)
OS	Windows 10 Professional
Display	12.5" anti-glare 10-point multi-touch FHD IPS display (1920x1080), brightness 320 nits
GPU	Intel® UHD Graphics 615
RAM	16 GB LPDDR3
SSD	512 GB PCIe NVMe
Network	WiFi IEEE 802.11a/b/g/n/ac: 2.4 GHz/5 GHz Gigabit-LAN Bluetooth® 4.1 Mobile data (microSIM): (3G Band: 1, 2, 4, 5, 6, 8, 19) (4G Band: 1, 2, 3, 4, 5, 7, 8, 12, 13, 17, 18, 19, 20, 21, 25, 26, 28, 29, 30, 38, 39, 40, 41, 66)
I/O	USB Type-C 3.1 Gen 1 USB Type-A 3.1 Gen 1 2x USB Type-A 2.0 HDMI VGA LAN RJ45 Audio out/mic in 3.5mm SD cardreader (SDHC/SDXC) up to 512 GB
Camera	Front: 2.07 MP (IR camera for Windows Hello)
Misc	GPS
Security	TPM 2.0, fingerprint, face recognition
Size	305.5 x 211.9 x 21 mm
Weight	approx. 1115 g, 623 g (dock), 492 g (tablet)
Material	Magnesium alloy, aluminium
Color	Black/silver
Accessoires	VAIO Digitizer Pen included (4096 pressure points)
Battery Runtime**	7.5 h
Warranty	24 months manufacturer warranty incl. pick-up and return service

* depending on model

** Runtime based on laboratory tests. Real world runtime can vary based on specifications and usage.

The battery in this product cannot be easily replaced by users themselves.
We reserve the right to make changes and corrections.