

ThinkVision T25m-10 61DCRAT1EU

Product

ThinkVision T25m-10

Region

EMEA

Color

Black

Panel

In-Plane Switching

Display Size

25"

View Area

535.45x338.76 mm

Resolution

1920x1200

Aspect Ratio

16:10

Pixel Pitch

0.2789x0.2823 mm

Dot / Pixel Per Inch

91 dpi

Brightness

300 nits

Contrast Ratio

1000:1

Pixel Response Time

4 ms (extreme mode) / 6 ms (normal mode)

Color Gamut

0.99

View Angle (H / V)

178 / 178

Stand

Tilt, Swivel, Height Adjust Stand

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

399.5x548.7x260.4 mm

Power Consumption (Typical / Maximum)

30W / 150W

Power Adapter

Integrated

Weight (Including Stand)

12.13 lb / 5.5 kg

Warranty

3-year

ENERGY STAR

ENERGY STAR 7.1

TCO

TCO 8.0

EPEAT

Bronze

Presets / User Settings

21/20

On Screen Display

OSD, 8 Languages

USB Port

USB 3.1 Gen1 x4

Speaker

3W X 2

Camera

None

Multiple Input

HDMI, DP, USB 3.1 Type-C

Monitor Cable

USB Type-C to Type-C

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Operating System

Support Windows 7, Windows 10

Ann Date (mm/yy)

06/19

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

ThinkVision T25m-10

DISPLAY

Panel Size
25.0 inches

Screen Dimensions (H x V)
535.45 x 338.76mm

Panel Type
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:10

Resolution
1920 x 1200 pixels

Pixel Pitch (H x V)
0.2789 x 0.2823mm

Viewing Angle (H x V)
178°/178°

Response Time (gray to gray)
4ms (extreme mode)
6ms (normal mode)

Contrast Ratio (typical)
1000:1

Dynamic Contrast Ratio (typical)
3M:1

Brightness (typical)
300 cd/m²

Color Gamut sRGB (CIE 1931)
99%

Color Support
16.7M

CONNECTIVITY

Video Input Signals
HDMI 1.4 + DP 1.2 + USB 3.1 Type-C™
(DP 1.2 Alt Mode)

Video Cables Supplied
USB 3.1 Type-C™

Video Cable Length
1.8m

USB Hub
Yes

USB Upstream
1 x USB 3.1 Gen1 (by USB Type-C™)

USB Downstream
4 x USB 3.1 Gen1 (with 1 BC)

Audio Out
Yes (3.5mm)

POWER

Power Consumption (Typical/Max)
30W/150W

Power Consumption Sleep/Off Mode
<0.5W

Power Consumption Switch Off-Mode
<0.3W

Power Supply
Internal

ENERGY STAR® (P_{on})
17.05W

ENERGY STAR® (E_{TEC})
63.12kWh

Power Voltage
100-240VAC (50/60Hz)

DIMENSIONS

Size Packed (D x H x W)
706 x 450 x 160mm/
27.79 x 17.72 x 6.30 inches

Size Unpacked w/stand (D x H x W) (mm/inch) (Lowest position)
260.4 x 399.5 x 548.7mm/
10.25 x 15.73 x 21.60 inches

Size Unpacked w/stand (D x H x W) (mm/inch) (Highest position)
260.4 x 509.5 x 548.7mm/
10.25 x 20.06 x 21.60 inches

Size Unpacked w/o stand (D x H x W) (mm/inch) (Head Only)
43.0 x 369.1 x 548.7mm/
1.69 x 14.53 x 21.60 inches

Weight Packed
7.8kg/17.20lbs.

Weight Unpacked
5.5kg/12.13lbs.

Weight (Monitor Head Only)
3.58kg/7.89lbs.

SPECIAL FEATURES

Anti-glare
Yes

Smart Power*
Yes

ThinkCentre Tiny Support
Yes

Optional Soundbar Support
Yes

Internal Speakers
Yes (3W x 2)

MECHANICAL

Tilt Angle (front/back)
-5°/30°

Swivel Angle (left/right)
+/-45°

Lift
Yes (110mm)

Pivot
+/-90°

VESA Mount Capability
Yes (100 x 100mm)

Kensington™ Lock Slot
Yes

Bezel Width (Side)
2.0mm

Bezel Width (top/bottom)
2.0/22.2mm

WHAT'S IN THE BOX

Monitor with stand
1 x Power Cable
1 x USB Type-C™ to Type-C™ cable
Quick Setup Guide

CERTIFICATIONS

ENERGY STAR® Rating
7.1

EU RoHS
Yes

CCC
Yes

TCO
TCO 8.0/TCO Edge 2.0

Windows Certification
Windows 7, Windows 10

China Energy Efficiency Standard
Tier 2

TÜV Eye Comfort
Yes

ULE
Gold



*The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to other devices. 75W power delivery by USB Type-C can be achieved when downstream USB ports are not connected and OSD brightness setting is <31.

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2019 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

ThinkVision T25m-10

