



Part No	90NB0MQ5-M02940
Model Name	UX434FAC-A5191T
EAN Code	4718017636667
UPC Code	192876636664
LCD Cover Color & Decoration	2B-Royal Blue, Bezel
Top Case Color & Decoration	2B-Royal Blue, Bezel
On board processor	Intel® Core™ i7-10510U Processor 1.8 GHz (8M Cache, up to 4.9 GHz)
Operating System	Windows 10 (64bit)
Office	Includes 1 month Trial for New Microsoft Office 365 Customers
Display	14.0'//Narrow border//300nits//FHD 1920x1080 16:9//Anti-Glare//sRGB: 100%//Wide View
Number Pad	N/A
ScreenPad™	ScreenPad™
Chipset	N/A
Memory Slot	N/A
Total System Memory	8GB on board
On board memory	8GB on board
Memory Max.	8G
How to upgrade memory	Not Available
Storage	PCIeG3x2 NVME 512GB M.2 SSD
EMMC/ISSD	N/A
External video display modes	HDMI 1.4
Discrete/Share	Share
IGPU	Intel UHD Graphics 620
Video memory	N/A
Video Camera	HD IR Camera
FingerPrint	N/A
On board Wireless	802.11ax+Bluetooth 5.0 (Dual band) 2*2
Card Reader	Type: Micro SD
USB Port	1x USB 2.0 1x USB3.1 Type A (Gen2) 1x USB3.1 Type C (Gen 2)
Interface	1x Headphone-out & Audio-in Combo Jack 1x HDMI 1.4
Audio	Built-in speaker Built-in array microphone Audio by ICEpower® harmon/ kardon
Weight (Kg)	1.10 KG (Without Battery) 1.15 KG (with 3 cell battery)

Dimension (cm)	31.9(W) x 19.9(D) x 1.69 ~ 1.82 (H) cm
AC Adapter	ø4.0 45W AC Adapter Output: 19V DC, 2.37A, 45W , Input: 100~240V AC 50/60Hz universal
Battery	50WHrs, 3S1P, 3-cell Li-ion
Replaceable Battery	No
Keyboard type	Illuminated Chiclet Keyboard
Software	McAfee Internet Security(Trial version)
Security	TPM (Firmware TPM)
Supplied Accessories	Sleeve

