



Part No	90NB0NM1-M00870
Model Name	UX534FAC-A8072T
EAN Code	4718017510301
UPC Code	192876510308
LCD Cover Color & Decoration	2B-Royal Blue, Bezel
Top Case Color & Decoration	2B-Royal Blue, Bezel
On board processor	Intel® Core™ i7-10510U Processor 1.8 GHz (8M Cache, up to 4.9 GHz)
Operating System	Windows 10 (64bit)
Office	Includes 1 month Trial for New Microsoft Office 365 Customers
Display	15.6'//Narrow border//300nits//FHD 1920x1080 16:9//Anti-Glare//NTSC: 72%//Wide View
Number Pad	N/A
ScreenPad™	ScreenPad™
Chipset	N/A
Memory Slot	N/A
Total System Memory	8GB on board
On board memory	8GB on board
Memory Max.	8G
How to upgrade memory	Not Available
Storage	PCIeG3x2 NVME 512GB M.2 SSD
EMMC/ISSD	N/A
External video display modes	HDMI 1.4
Discrete/Share	Share
IGPU	Intel UHD Graphics 620
Video memory	N/A
Video Camera	HD IR Camera
FingerPrint	N/A
On board Wireless	802.11ax+Bluetooth 5.0 (Dual band) 2*2
LAN	N/A
Card Reader	Type: Standard SD
USB Port	1x USB3.1 Type A (Gen1) 1x USB3.1 Type A (Gen2) 1x USB3.1 Type C (Gen 2)
Interface	1x Headphone-out & Audio-in Combo Jack 1x HDMI 1.4
Audio	Built-in array microphone Audio by ICEpower®
Weight (Kg)	1.20 KG (Without Battery) 1.65 KG (with 8 cell battery)

Dimension (cm)	35.4(W) x 20.0(D) x 1.89 ~ 1.89 (H) cm
AC Adapter	ø4.5 65W AC Adapter
Battery	Output: 19V DC, 3.42A, 65W . Input : 100~240V AC, 50/60Hz universal 71WHrs, 4S2P, 8-cell Li-ion
Replaceable Battery	No
Keyboard type	Illuminated Chiclet Keyboard
Software	McAfee Internet Security(Trial version)
Security	TPM (Firmware TPM)
Supplied Accessories	Sleeve
Warranty	2 years Carry-In Germany and Austria

