

KERN PNJ3000-2M

The new standard in the laboratory with robust tuning fork measuring system



Minimum piece weight at piece counting (Normal):	100 mg
--	--------

Functions

Capacity display:	yes
Counting function:	yes
Percentage determination:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	5 °C

Power supply

Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter:	Mains adapter external
Mains adapter/adapter included:	CH EURO UK US

Service

DAkkS Certificate:	963-127
Verification:	965-216

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	321 x 410 x 220 mm
Gross weight:	4,600 kg
Net weight:	3,500 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	196 x 293 x 89 mm
Dimensions of weighing plate (WxDxH):	190 x 190 x 89 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	190 x 190 mm

Measuring system

Adjustment options:	Internal calibration (manual)
Linearity:	20 mg
Minimum weight (USP):	20 g
Readability [d]:	10 mg
Repeatability:	10 mg
Resolution:	320000
Stabilisation time under laboratory conditions:	3 s
Tare range:	3,200 kg
Warm up time:	2 h
Weighing capacity [Max]:	3,200 kg
Weighing units:	ct dwt g lb mo oz ozt tl (HK) tl (Singap. Malays) tl (Tw) tol

Display

Display digit height:	1,650 cm
-----------------------	----------

Technical data about verification

Minimum load [Min]:	500 mg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	II
Verification value [e]:	100 mg

Counting

Counting resolution:	320000
Minimum piece weight at piece counting (Laboratory):	10 mg


KERN PNJ3000-2M



The new standard in the laboratory with robust tuning fork measuring system

Piktogramme

STANDARD



OPTION



FACTORY

