




M2R **PRO** WARRIOR

Deliberate Tactical Operation

MAX OUTPUT	MAX RUNTIME	MAX THROW
		
1,800 lumens	50 days	300 meters



M2R PRO

M2R Pro is the next level in tactical flashlights.

It is powerful, delivering an 1,800-lumen output and a 300-meter throw; high output
via a 5000mAh 21700 rechargeable battery.

It is tactical; easily concealed with a quiet tail switch.

It is an excellent defensive tool with an aggressive strike bezel.

It provides firm grip with a new designed body texture.

It is easy to operate with a raised tail switch.

It is versatile; handheld and weapons mountable via a magnetic remote
pressure switch.





Powerful to deliver an 1,800-lumen output and a 300-meter throw



High output via a 5000mAh 21700 rechargeable battery, supporting a maximum runtime of 50 days @moonlight mode



- Easily concealed with a quiet tail switch
- Easy to operate with a raised tail switch



Great feeling of firm grip with a new designed body texture



Excellent defensive tool with an aggressive strike bezel



Handheld and weapons mountable via a magnetic remote pressure switch



MARKET APPLICATIONS

Tactical / Self-defense / Outdoors

UPC: 697237812047 2

MSRP: \$109.95

DESCRIPTION




OUTPUT

SPECIFICATION	Mode 1	Mode 2	Mode 3	Mode 4	Mode 5	Mode 6
	1,800 \pm 750 \pm 250 lumens	750 \pm 250 lumens	250 lumens	60 lumens	15 lumens	1 lumens
	4.5+145+45 minutes	160+40 minutes	10 hours	40 hours	130 hours	50 days
	300 meters	185 meters	110 meters	55 meters	27 meters	N/A
	22,400 cd	8550 cd	3000 cd	750 cd	180 cd	N/A
	13 Hz at 1800 lumens					

The above data are test results retrieved according to ANSI NEMA FL 1-2009 standards.

WATERPROOF IPX8



DROP TEST



COMPLIANCE



LIGHT SOURCE

High performance neutral white LED

DIMENSIONS

Length: 5.37in/136.50mm

Head Diameter: 1.16in/29.50mm

Body Diameter: 1.03in/26.20mm

WEIGHT

6.31oz/179g (including battery and pocket clip)

BODY MATERIAL

AL6061-T6 aluminum alloy

POWERED BY

Customized 5000mAh 21700 rechargeable lithium battery

WARRANTY

Olight's 5 Years Warranty

Visit: <https://olightworld.com/olight-warranty>

IN THE BOX

M2R Pro Warrior Flashlight x 1
Customized 5000 mAh 21700 Rechargeable Lithium Battery X 1 (Included)
MCC3 Magnetic USB Charging Cable X 1
Stainless Steel Pocket Clip X 1
Lanyard X 1
Holster X 1
User Manual x 1

OPTIONAL ACCESSORIES

RWX07 7" Linear Wire Magnetic Remote Switch (for Long Gun)

RWX Long Coil Wire Magnetic Remote Switch (for Shotgun)

SK2 Flashlight Holster