



# Baton Pro

Pocket Sized Colossal Power

MAX OUTPUT	MAX RUNTIME	MAX THROW
		
2,000 lumens	9 days	132 meters



# Baton Pro

Pocket Sized Colossal Power



## MARKET APPLICATIONS

Camping & Hiking & Mountaineering  
Home

UPC:

697237812034 2

## DESCRIPTION

The Baton Pro is the newest version of our portable, rechargeable side-switch LED flashlight. Powered by a single 3500mAh 18650 customized lithium rechargeable battery and a high-efficiency LED, the Baton Pro delivers a maximum output of 2000 lumens. The Baton Pro adopts OLIGHT's signature magnetic USB charging system for a more convenient charging station. With increased output and easier charging, the Baton Pro provides a high-performance portable experience for outdoor lighting.



## FEATURES

- Delivers a maximum output of 2,000 lumens with cool white high performance LED available.
- The Baton Pro, with an 18mm diameter TIR lens, is 28% larger than that of the previous generation, providing better light quality with a soft and balanced beam.
- The Baton Pro adopts 3D small squared and big rounded texture milling pattern for an extremely firm grip and great look.
- The blue dual-directional stainless steel pocket clip can easily attach to your backpack, belt or pocket for easy access.
- Visual display indicator located on the center of the switch to clearly display the battery level in real time.

## OUTPUT

STANDARD	Mode 1	Mode 2	Mode 3	Mode 4	Mode 5	Strobe
	*2,000 z 600 lumens	600 lumens	120 lumens	30 lumens	5 lumens	13Hz at 2000 lumens
	1+160 minutes	210 minutes	810 minutes	55 hours	9 days	
	132 meters	70 meters	30 meters	15 meters	N/A	
	4,350 cd	1,220 cd	220 cd	50 cd	N/A	

Note:

- (1) All data above are test results according to ANSI NEMA FL 1-2009 standards.
- (2) The data above uses the standard 3500mAh 18650 rechargeable battery, and is measured indoors under a room temperature of 25 degrees Celsius with windless conditions. Normal use performance may vary depending on the actual environmental temperature and ventilation conditions.

## LIGHT SOURCE

One High Performance Cool White LED

## DIMENSIONS

Length: 4.25in/108mm  
 Head Diameter: 0.98in/25mm  
 Body Diameter: 0.94in/24mm

## WEIGHT

3.77oz/107g ( including pocket clip and battery)

## BODY MATERIAL

6061-T6 Aluminum Alloy(main body)

## POWERED BY

Customized 3500mAh 18650 (included)

## WARRANTY

Olight's 5 Years Warranty  
 Visit: <https://olightworld.com/olight-warranty>

## IN THE BOX

Flashlight (Stainless Steel Blue Clip Included) X 1  
 Customized 3500mAh 3.6V 18650 Lithium Rechargeable Battery X 1(Installed In The Flashlight)  
 MCC 1A Magnetic USB Charging Cable X 1  
 PouchX1  
 Lanyard (with a pin tool) X 1  
 User Manual X 1

### WATERPROOF IPX8



### DROP TEST



### COMPLIANCE

