




# Perun

Multi-functional Reliable Right Angle Light

MAX OUTPUT	MAX RUNTIME	MAX THROW
		
2,000 lumens	10 days	120 meters



▲  
Blue (Limited Edition)



▲  
Black

## MARKET APPLICATIONS:

Outdoors  
Household

UPC: 697237812056 4 (Black)

697237812067 0 (Blue)

## DESCRIPTION


Perun is a multi-functional illumination tool powered by a 3500mAh 18650 battery with a maximum output of 2,000 lumens. This compact, hands-free right-angle light boasts the third generation MCC which holds 1.5A current. When the built-in infrared distance sensor detects an obstruction nearby, the brightness will automatically be reduced to the lowest level for protection. Perun can be used as a handheld light with the provided pocket clip for a variety of attachment methods as well as a headlamp with the optional magnetic head strap, making it a powerful, reliable and vital tool for multiple activities in the dark.



## FEATURES

- **Multi-functional Use:** Features a right-angle head, stainless steel pocket clip and magnetic base for a variety of hands-free attachment methods to the body, backpack, hat or steel components, quick and easy.
- **Powerful Performance:** Powered by a 3500mAh 18650 rechargeable battery with a maximum output of 2,000 lumens; equipped with incredible MCC3 charging cable for 50% faster charging than H2R.
- **Reliable and Trustworthy:** When the built-in infrared distance sensor detects an obstruction nearby, the brightness will automatically be reduced to the lowest level for protection.
- **Immersive Experience:** The intuitive operation provides a convenient experience for different applications, and all-new designed compact body for an extremely firm grip.


## OUTPUT

SPECIFICATION	MODE 1	MODE 2	MODE 3	MODE 4	MODE 5
	2,000 ± 800 lumens	500 lumens	120 lumens	30 lumens	5 lumens
	2.5+160 minutes	240 minutes	15 hours	47.5 hours	10 days
	120 meters	60 meters	30 meters	16 meters	N/A
	3600 cd	900 cd	220 cd	65 cd	N/A

Note:

- (1) All data above are test results according to ANSI NEMA FL 1-2009 standards.  
 (2) The data above uses the standard 3500mAh 18650 rechargeable battery, and is measured indoors under a room temperature of 25 degrees Celsius with windless conditions. The runtime of turbo and high modes may vary depending on the external temperature and ventilation conditions.

### WATERPROOF IPX8



### DROP TEST



### COMPLIANCE



## LIGHT SOURCE

One High Performance Cool White LED

## DIMENSIONS

Length: 4.41in/112mm  
 Head Diameter: 1.02in/26mm  
 Body Diameter: 0.91in/23mm

## WEIGHT

4.23oz/120g (Including Battery)

## BODY MATERIAL

Aluminum Alloy(Main body)

## POWERED BY

Customized 3500mAh 18650 Battery (Included)

## WARRANTY

Olight's 5 Years Warranty  
 Visit: <https://olightworld.com/olight-warranty>

## IN THE BOX

Perun(Battery Included) x 1  
 Stainless Steel Pocket Clip x 1  
 MCC3 Magnetic Charging Cable x 1  
 Lanyard x 1  
 User Manual x 1

## OPTIONAL ACCESSORIES

Head Strap and Mount  
 15A 3000mAh Rechargeable Lithium Battery