


Seeker 2

Simply Powerful

MAX OUTPUT	MAX RUNTIME	MAX THROW
		
3,000 lumens	15 days	220 meters



MARKET APPLICATIONS

Household & Outdoors & Law Enforcement

UPC: Seeker 2 (Black) 697237812027 4

Seeker 2 (Blue) 697237812043 4

DESCRIPTION

Powered by a single 21700 (5000 mAh) customized lithium rechargeable battery, the Seeker 2 delivers a maximum output of 3,000 lumens. Using three highly efficient OSRAM LEDs paired with a TIR optic lens help to provide a perfect medium and close-range illumination experience. The Seeker 2 features a large side switch, located near the head of the light, for comfortable thumb operation. The indicator built into the center of the switch clearly displays the remaining battery power with a green, orange or red color. The contoured grooves on the surface of the aluminum alloy body is designed to provide a comfortable non-slip grip. Compatible with most USB power sources, the magnetic charging cable is convenient to use, making the Seeker 2 a perfect illumination tool to be used at home, outdoors, or on duty.



FEATURES

- Paired with three highly efficient cool white LEDs, delivering a maximum output of 3,000 lumens and a beam distance of 220 meters.
- The contoured grooves on the surface of the aluminum alloy body is designed to provide a comfortable non-slip grip.
- Visual display indicator located on the center of the switch clearly displays the battery level in real time.
- Includes a high efficient portable magnetic charger with a faster 1A current charging speed.
- The provided 1.5mm lanyard is not only convenient and comfortable for use, but can last for a very long time.

OUTPUT

STANDARD	Mode 1	Mode 2	Mode 3	Mode 4	Mode 5
	3,000 ± 600 lumens	1,200 ± 600 lumens	300 lumens	50 lumens	5 lumens
	3+155 minutes	110+50 minutes	13 hours	72 hours	15 days
	220 meters	135 meters	68 meters	28 meters	10 meters
	12,100 cd				
	13 Hz @3000 lumens				

WATERPROOF IPX8



DROP TEST



COMPLIANCE



The above data are test results retrieved according to ANSI NEMA FL 1-2009 standards.

LIGHT SOURCE

Three high performance cool white LED

COLOR

Black and Blue

DIMENSIONS

Length: 4.96in/126mm

Head Diameter: 1.38in/35mm

Body Diameter: 1.08in/27.5mm

WEIGHT

6.53oz/185g (including battery)

BODY MATERIAL

AL6061-T6 Aluminum Alloy

POWERED BY

Customized 21700, 5000mAh 3.6v Battery

WARRANTY

Olight's 5 Years Warranty

Visit: <https://olightworld.com/olight-warranty>

IN THE BOX

Flashlight (Battery Included) X 1
0.5 Meter MCC1A Magnetic Charging Cable X 1
Lanyard X 1
User Manual X 1

OPTIONAL ACCESSORIES

L-DOCK KIT: including the L-dock and 1.2 meters MCC1AL magnetic USB charging cable X 1
Flashlight clip x 1
Traffic wand x 1