



SURFTAB TWIN 10.1 (2019)

Hardware

Processor (CPU)	Intel® Celeron® N4000 Prozessor (bis zu 2.6 GHz, 4MB Intel® Smart-Cache) Dual-Core
Operating system	Windows 10 Home in S mode
Office	Office 365 Personal (one-year-license) ¹
RAM	4 GB
Internal storage	64 GB ²
Graphic Unit (GPU)	Intel® UHD Graphics 600
Display size	25.7 cm (10.1")
Display type	10-point capacitive multi-touch HD IPS display
Screen resolution	1280 x 800 pixel
Aspect ratio	16:10
Camera	Front: 0, 3 MP, Rear: 2 MP
Speaker	yes
Microphone	yes
Interface	2 x USB 3.1 Gen 1, 1 x Mini-HDMI®, audio out/mic in (3.5 mm), memory card reader, tablet dock, keyboard dock
Network	WiFi, Bluetooth 4.2, Miracast™
Frequencies	WiFi IEEE 802.11ac/b/g/n: 2.4 GHz/5 GHz
Memory extension	microSD(HC/XC) up to 128 GB
Dimensions	approx. 260 mm x 174 mm x 10 mm
Weight	approx. 1157 g (tablet & keyboard), approx. 621 g (tablet), approx. 1778 g (total)
Housing material	Plastic (Rubber)
Color	Black

SURFTAB TWIN 10.1 (2019)

Battery and power supply

Type of battery	Lithium polymer
Capacity of battery	7,4 V / 3000 mAh / 22,20 Wh
Charge by	DC IN
Power supply	230 V (110 V - 240 V)

Other characteristics

More	G-sensor, Hall-sensor
Languages	German, English, Italian, Spanish, French, Dutch
Package contents	Surftab® twin 10.1, power adapter (100 V - 240 V), cleaning cloth, quick guide, important safety and legal information

Operation and storage

Temperatures	5° C to 30° C
Relative humidity	30 % to 70 %

¹Office 365 Personal for 12 months included, software is already pre-installed. Office activation is required within 6 months of Windows activation date. After expiration, the license must be renewed for a fee.

²1 GB = 1 000 000 000 Bytes.

Memory card not included in the delivery.

We reserve the right to make changes and corrections.

The battery in this product cannot be easily replaced by users themselves.