

KODAK PIXPRO AZ528

DIGITAL CAMERA



AZ528 ASTRO ZOOM

Beauty is in the eye of the beholder with the KODAK PIXPRO AZ528 Astro Zoom Camera. Now better than ever, all the power and performance you could wish for is harnessed in this cutting-edge, mega zoom bridge camera. Amazing detail, plenty of features and 52x optical zoom that get you nice and close are just the beginning. Explore the power and freedom the AZ528 affords you first hand. KODAK PIXPRO Digital Cameras – Tell your story.

FEATURES:

- 52x Optical Zoom
- 24mm Wide Angle
- 16 MP CMOS
- 6 fps Burst Shooting
- 3" LCD
- Wi-Fi® Connection
- Wirelessly Control with your iOS™/ANDROID™ Device

52X
Optical
Zoom

24mm
WIDE

16MP BSI
CMOS

3" LCD

OIS

Panorama
Capture



Available Colors:

 MIDNIGHT BLUE



KODAK PIXPRO AZ528

DIGITAL CAMERA

SPECIFICATIONS	AZ528
Effective Image Sensor Pixels	16.35 Megapixels
Total Image Sensor Pixels	16.76 Megapixels [1/2.3" BSI CMOS]
Lens	
Focal Length	4.3 mm (Wide) — 223.6 mm (Tele)
[35mm film equivalent]	[24 mm (Wide) — 1248 mm (Tele)]
F number	F2.8 (Wide) — F5.6 (Tele)
Lens Construction	13 groups 15 elements
Compatible Filter Diameter	Ø52mm
Optical Zoom	52x
Focusing Range	Normal: (Wide) 60 cm — ∞, (Tele) 300 cm — ∞ Macro: 1 cm — ∞ (Wide Only)
Electronic Viewfinder	No
Anti-Handshake	OIS (Optical Image Stabilization)
Digital Zoom	4x Digital Zoom (Combined Zoom: 208x)
Number of Recording Pixels	
Still Image	(4:3) 16MP: 4608x3456, 10MP: 3648x2736, 5MP: 2592x1944, 3MP: 2048x1536, 0.3MP: 640x480, (3:2) 14MP: 4608x3072, (16:9) 12MP: 4608x2592, 2MP: 1920x1080
Movie	1920x1080: 30fps, 1280x720: 60fps / 30fps, 640x480: 30fps; High-Speed Movie 640x360: 120fps
Image Compression	Best, Fine, Normal
DCF, DPOF (Ver1.1) Support	Yes
File Format	
Still Image	Exif 2.3 (JPEG)
Movie	MOV [Image: H.264, Audio: Linear PCM (Stereo)]
Shooting Modes	Auto, P, S, A, M, Face Beautifier, Wi-Fi®, SCN, Movie, CS
SCN Modes	Panorama, Children, Portrait, Night Portrait, Handheld Night, Landscape, Sport, Sunset, Fireworks, Multi Exposure, Snow, Party, Pet
Photo Touch-up	Red-Eye Removal, Skin Soften, Eye Brightening, Eye Enlargement
Detection Features	Face, Smile, Blink, Cat, Dog
HDR	Yes
Panorama	Up to 360°
LCD Display	3.0 inch (460K Pixels)
ISO Sensitivity	Auto, ISO 100/200/400/800/1600/3200
AF Method	Single AF, Multi-AF (TTL 25-point), Object Tracking, Face Detection
Exposure Metering Method	Artificial Intelligence AE (AiAE), Center-Weighted Average, Spot (Fixed to Center of Frame), Face AE
Exposure Control Method	Program AE (AE-Lock Available), Aperture Priority AE, Shutter Priority AE
Exposure Compensation	+/- 3EV in 1/3 Step Increments
Shutter Speed	1/2000 – 30 Seconds (Mechanical and Electronic Shutter)
Continuous Shooting	Approx. 6 fps (Full Resolution)
Playback Modes	Single, Index (9/16 Thumbnails) Slide Show, Date, Burst Shooting, Zoom (Approx. x2 – x8)
White Balance Control	Auto (AWB), Daylight, Cloudy, Fluorescent, Fluorescent CWF, Incandescent, Manual, Color Temperature Setting (1900K ~ 10000K)
Flash	
Flash Method	Pop-up (Manual)
Flash Modes	Auto, Red-Eye Reduction, Fill Flash, Force Off, Slow Synchro, Red-Eye Reduction + Slow Synchro
Shooting Range	(Wide) Approx. 0.5 m – 7.5 m (ISO800); (Tele) Approx. 1.2 m – 3.7 m (ISO800)
Recording Media	Internal Memory: Approx. 8MB SD/SDHC Card (Up to 32GB Support) [MMC Card not supported] (Class 4 Card or better recommended)
Other Features	Wi-Fi® (802.11 b/g/n), Remote Control (via iOS™/ANDROID™ Device) Multi-Language Support (27 Languages)
Jacks	AV-OUT/USB 2.0 (Micro 5 pin USB)
Power	Rechargeable Li-ion Battery (LB-060), 3.7V 1100mAh, In-Camera Charging
Shooting Capability (Battery Performance)	Approx. 240 Shots (Based on CIPA Standards)
Operation Environment	Temperature: 32° – 104°F / 0° – 40°C, Humidity: 0 – 90%
Dimensions (WxHxD)	Approx. 4.96 x 3.51 x 4.48 in. / 121.3 x 85.8 x 97.5 mm (Based on CIPA Standards)
Weight	Approx. 17.92oz / 508g (Body Only)
Supplied Accessories	Rechargeable Li-ion Battery, AC Adapter, USB Cable, Neck Strap, Lens Cap, Service Card, Quick Start Guide, Warranty Card

JK Imaging Ltd.

To learn more about KODAK PIXPRO Digital Cameras:
visit: kodakpixpro.com

17239 So. Main Street, Gardena, CA 90248 (888) 978-0806

© 2019 JK Imaging, Ltd. The Kodak trademark, logo and trade dress are used under license from Eastman Kodak Company.
All information contained in this document is subject to change without notice. Document Number/Sequence: U.DIS.0060.0419.en.01

