



Order symbol: TPC 191209T
Product nbr: 5824005
Description: Enclosure, PC
Remarks: Clear transparent cover

EAN: 6418074048646
EI. number:
Finland:

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	187	122	90	MIV 10	DIN-35 Mounting rail
inch:	7.4	4.8	3.5	DH-3	DIN-35 Mounting rail
				FP 10674	
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP65	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07/IK08	
Cover screws material:	Polyamide			Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey			Flammability Rating: UL 746C 5"	
Gasket material:	Polyurethane			Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 4, 4X, 12	
Temperatures:				Certificates:	
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko	
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 250 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
MP 1912	Mounting plate				

