



HRA-600D+

DAB+ / FM HOME RADIO WITH HEADPHONES OUT.

DAB+
Digital Audio Broadcasting



HRA-600D+/WD



HRA-600D+/WH

HOME RADIO

HRA-600D+

DAB+ / FM HOME RADIO WITH
HEADPHONES OUT.



CD PLAYER

Loader type
Electronic Shock Protection
Compressed audio playback
Disc support
Auto ID3 tag detection
MP3 search by
Data rate system
Fast forward / reverse
Track search
Intro scan
Random play
Repeat track / album
Program function

TUNER

Tuner type	Digital
Ranges (band)	DAB / DAB+ / FM
RDS system / Radiotext	•
Preset stations	10 + 10
Stereo / Mono selector	(Mono)
Automatic tuning	•
Manual tuning	•

CASSETTE

Cassette deck
Cassette mechanism
Automatic Level Control (ALC)
One Touch Recording (OTR)
Built-in microphone

USB/SD/MMC

Encoding
Playback
Copy
Delete
iPod compatibility

TURNTABLE

R.P.M.
Tone Arm Mechanism

CONNECTIONS

Bluetooth	
USB port	
Card slot	
Aux in	
Line Out	
Headphones socket	Ø 3.5mm Jack

AUDIO

Speaker system	1 speaker
Total PMPO Output Power	24 Watt
Nominal Output Power	1 x 3 Watt rms
Volume control	Encoding
Preset equaliser	

GENERAL

Accessories included	AC/DC adaptor
Colour Versions	WD - Wood WH - White
Display / Illumination	LCD
Power supply	230V AC
Battery Memory	
Weight	0.7 Kg
Dimensions (WxLxH)	140x140x200 mm

COMMERCIAL

Container load 40'	10'200 pcs
Container load 20'	5'004 pcs
Shipping carton	12 pcs
Gift Box size (WxLxH)	150x150x212 mm
Shipping car. size (WxLxH)	315x465x445 mm

EAN code

HRA-600D+/WD	7621800032737
HRA-600D+/WH	7621800032744

Master Carton EAN code

HRA-600D+/WD	7621800054647
HRA-600D+/WH	7621800054654
Country of origin	P.R.C.