




# TRA-1957N

VINTAGE STYLE AM / FM PORTABLE RADIO  
WITH HEADPHONES OUT.



TRA-1957N/CR

TRA-1957N/WD

**PORTABLE RADIO**

# TRA-1957N

VINTAGE STYLE AM / FM PORTABLE RADIO  
WITH HEADPHONES OUT.



## CD PLAYER

Loader type
Electronic Shock Protection
Compressed audio playback
Disc support
Auto ID3 tag detection
MP3 search by
Data rate system
Fast forward / reverse
Track search
Intro scan
Random play
Repeat track / album
Program function

## TUNER

Tuner type	Analog
Ranges (band)	AM / FM
RDS system / Radiotext	
Preset stations	
Stereo / Mono selector	(Mono)
Automatic tuning	
Manual tuning	•

## CASSETTE

Cassette deck
Cassette mechanism
Automatic Level Control (ALC)
One Touch Recording (OTR)
Built-in microphone

## USB/SD/MMC

Encoding
Playback
Copy
Delete
iPod compatibility

## TURNTABLE

R.P.M.
Tone Arm Mechanism

## CONNECTIONS

Bluetooth	
USB port	
Card slot	
Aux in	
Line Out	
Headphones socket	Ø 3.5 mm Jack

## AUDIO

Speaker system	1 speaker
Total PMPO Output Power	10 Watt
Nominal Output Power	1 x 1.2 Watt rms
Volume control	Analog
Preset equaliser	

## GENERAL

Accessories included	AC Cable
Colour Versions	WD - Wood CR - Cream

Display / Illumination	
Power supply	230V AC / 6 x "LR14" Batteries

Battery Memory	
Weight	2 Kg
Dimensions (WxLxH)	335x85x235 mm

## COMMERCIAL

Container load 40'	3396 pcs
Container load 20'	1698 pcs
Shipping carton	6 pcs
Gift Box size (WxLxH)	385x155x230 mm
Shipping car. size (WxLxH)	470x530x397 mm

## EAN code

TRA-1957N/WD	7621800026514
TRA-1957N/CR	7621800030375

## Master Carton EAN code

TRA-1957N/WD	7621800050229
TRA-1957N/CR	7621800052346
Country of origin	P.R.C.