






Denver IR-140

- Internet Radio in wooden housing
- WiFi connection
- UPnP and DLNA compatible streaming
- Plays bluetooth music
- 4 Quick access favorite buttons
- 99 Presets for favorite stations
- Built in rechargeable battery 3.7V 2000mAh
- 7-8 hours play time on WiFi at 50% volume level (subject to the backlight set to dim level 10%)
- 2.4" color TFT
- 2 rotary knobs - One for volume and one for tune/select
- Dimmer setting: completely dark mode is available
- Sleep timer
- Dual alarm clock (use only when power is connected)
- Audio output 3W RMS x 1
- 3.5 mm Headphone jack (stereo)
- 3.5 mm Line out jack (stereo)
- USB charging cable and power plug included



-  Highlights
Internet radio, Wi-Fi connection, Clock & alarm function, DLNA/uPnP streaming from own network
-  Power
230V power adaptor included
-  Battery
Built in rechargeable battery 3.7V 2000mAh
-  WIFI
Built-in Wi-Fi function
-  Tuners
Internet radio

Shipping information

Unit size: 18.50(w) x 12.00(d) x 11.80(h) cm

Gross weight: 1.15

Giftbox size: 27.70(w) x 15.10(d) x 16.00(h) cm

4 Pcs./export carton

3360 Pcs./20' container

8160 Pcs./40' HQ container

Barcode: 5706751051296