DIGITUS®

4-PORT UNIVERSAL USB CHARGING ADAPTER, USB-C™ / USB A, 100 W



Quick Installation Guide DA-10197

INTRODUCTION

With the DIGITUS® Universal Charging Adapter, two USB-C™ devices and two USB A devices can be charged simultaneously. Compatibility with Power Delivery 3.0 (PD) enables rapid charging with up to 100 W for both USB-C™ ports and 30 W for both USB A ports. In combined operation, an output of 65 W is available for USB-C™ devices and 30 W in total for USB A devices. Charge tables, smartphones mobile gaming consoles and even notebooks with the highest possible output. The integrated security features such as short circuit, surge and excess heat protection ensure the safety of your devices.

PACKAGE CONTENT

- 1 x 4-Port Universal USB Charging Adapter, USB-C[™] / USB A, 100
 W
- 1 x USB cable (USB-C[™] USB-C[™], 1 m)
- 1 x QIG

SECURITY ADVISE

Please read the following information before usage:


- Do not touch this product with wet hands or expose it to water
- Prevent the USB ports from conductive materials, such as liquids, dust, metal powders, and pencil leads
- If you are not using it for longer time, disconnect the charger from the power socket
- This product is intended for private use only and shouldn't not be used for commercial purposes to prevent material damage or personal injuries.
- Do not use this product in any way other than for the intended usage

- · For indoor use only
- Do not expose to water or excessive moisture
- Do not use the product if the ambient temperature exceeds 25°C
 Do not store outside the temperature range 0-40°C
- · Do not drop, damage or disassemble this product
- · Do not use this product it is damaged in any way
- If the product becomes unusually hot, stop using it immediately and contact customer support
- There is a risk of electric shock if the product is used incorrectly
- Not suitable for use by children or use by persons with reduced physical, sensory or mental capabilities, or lack of experience or knowledge, unless they have been given supervision or instruction concerning use of the product by a person responsible for their safety

PRODUCT FEATURES

- Charge mobile devices like notebooks, tablets or smartphones with up to 100 W (USB-C™)
- Use of all 4 ports simultaneously is possible
- Supports Power Delivery (PD 3.0)
- Ultra-compact also suitable for use on the go
- Surge protection, short circuit protection and overheating protection
- LED charging indicator light
- 2 x USB-C[™] port with a total charging capacity of 100 W
- 2 x USB A ports with a total charging capacity of 30 W
- Combined operation USB-C[™] 65 W / USB A 30 W

PRODUCT OVERVIEW



TECHNICAL SPECIFICATIONS

- Number of USB-C[™] ports: 2
- Number of USB A ports: 2
- Output of USB-C™ ports: 100 W max. for both ports in total
- · Power output USB A ports: 30 W max. for both ports in total
- When using USB-C™ and USB A ports simultaneously:
 USB-C™ 65 W max. in total / USB A 30 W max. in total
- Supported output voltages in volts: 5 / 9 / 12 / 15 / 20
- Input voltage: 100 240 V AC, 50/60 Hz, 2 A
 Mains plug: CEE-7/16 Euro plug (Type C)
- Walls plug. CLL-7/10 Lul 0 plug (Type
- Dimensions: L75 x W 75 x H 28.7 mm
- Weight: 200 g
- Color: White

POWER SPECIFICATIONS

Input: 100-240 VAC, 50/60 Hz, 2 A max.

Output: 2x A QC 3.0 (30 W x 2), 2x C (100 W max each port)

Detailed Output information

Output: USB-C™ 1: 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/5A max.

USB-C™ 2: 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/5A max.
USB-A 1: 4.5V/5A, 5V/4.5A, 9V/3A, 12V/2.5A, 20V/1.5A max.

USB-A 2: 4.5V/5A, 5V/4.5A, 9V/3A, 12V/2.5A, 20V/1.5A max.

In combined output usage:

USB-C[™] 1 + USB-C[™] 2 65W + 30W = 95W USB-C[™] 1 + USB-A 1 65W + 30W = 95W

USB-C[™] 1 + USB-A 1 65W + 30W = 95W USB-C[™] 1 + USB-A 2 65W + 30W = 95W

USB-C™ 1 + USB-A 1 + USB-A 2 65W + 7.5W + 7.5W = 80W

USB-C[™] 2 + USB-A 1 65W + 30W = 95W


USB-C™ 2 + USB-A 2 65W + 30W = 95W USB-C™ 2 + USB-A 1 + USB-A 2 65W + 7.5W + 7.5W = 80W USB-C™ 1 + USB-C™ 2 + USB-A 1 45W + 30W + 18W = 93W

USB-CTM 1 + USB-CTM 2 + USB-A 2 45W + 30W + 18W = 93W

USB-C™ 1 + USB-C™ 2

+ USB-A 1 + USB-A 2 45W + 30W + 7.5W + 7.5W = 90W

USAGE



- When the AC plug is connected to the power socket and the LED indicator lights up, it means the product is powered on
- Connect the device and the charging adapter with a charging cable.

RECYCLING

This symbol on the electronic product or on its packaging indicates that the electronic product (including the battery) should not be treated as household waste. Instead, it should be handed over to the appropriate collection point for the recycling of electrical and electronic equipment. Do not attempt to remove internal baiteries. Internal batteries shall be removed only by a waste treat mentfacility or trained service professional.



By ensuring this product is disposed of correctly, you will help prevent potential negative consequences, for the environment and human health, which could otherwise be caused by inappropriate waste handling of this product. The recycling of materials will help conserve natural resources. For more information about recycling of this product, please contact your local council for advice or your household waste disposal service.

DISCLAIMER

Hereby Assmann Electronic GmbH, declares that the Declaration of Conformity is part of the shipping content. If the Declaration of Conformity is missing, you can request it by post under the below mentioned manufacturer address.

www.assmann.com

Assmann Electronic GmbH Auf dem Schüffel 3 58513 Lüdenscheid, Germany

