



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #3-1393480-7
D-Sub Receptacle Assy: Eurostyle, Right Angle, 2.74mm



TE Part #2-167495-4
48P.IEC-F MALE CONN



TE Part #2-106506-2
D-Sub Receptacle Assembly: Right Angle, Shell Size 2, 2.74mm



TE Part #100108-4
32P.IEC-F FEM.CONN.



TE Part #1393644-9
V42254B1100C480=PC612 MESSERLE

TE Part #1825290-6
MHS233GRA04=DP3T SL SW R/A AU

TE Part #1834039-6
Header Recp., 2mm, 6 POS, GOLD FLASH

TE Part #2-828296-0
20P MOD 2 STIFT LEI

TE Part #3-100318-2
DUAL LOADED

TE Part #966260-1

Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1571650-4_D3.3d_igs.zip

English

Customer View Model

ENG_CVM_1571650-4_D3.3d_stp.zip

English

Customer View Model

ENG_CVM_1571650-4_D3.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

Instruction Sheets

Instruction Sheet (U.S.)

English